

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [\*\*1300980117\*\*](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male with O-Ring, Cable Diameter 14.27-17.45mm (.562-.687")

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR32159
UL	E76954

**General**

Product Family	Cable Grips
Series	<a href="#">130098</a>
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 6P
O-Ring	Yes
Overview	<a href="#">Strain-Relief Cord Grips</a>
Product Literature Order No	987651-6081
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855412
Use With	3/4" NPT MAX-LOC Lock Nut <a href="#">1300990144</a>

**Physical**

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	14.27-17.45mm (.562-.687")
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
Thread Size	3/4" NPT

**Material Info**

Engineering Number	5541W
--------------------	-------



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130098 Series](#)