

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300980185](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** MAX-LOC Strain Relief Cord-Sealing Grip for UF Cable, 1/2" NPT, Straight Male, Cable Diameter 5.54x10.69mm (.218x.421") Oval

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR32159  
UL E76954

**General**

Product Family Cable Grips  
Series [130098](#)  
Exclude SD Check Yes  
Eye Type N/A  
NEMA Rating NEMA 3R  
O-Ring No  
Overview Strain-Relief Cord Grips  
Product Literature Order No 987651-6081  
Product Name MAX-LOC  
Type Strain Relief Grip  
UPC 78678872144  
Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#) , MAX-LOC O-Ring, 1/2" NPT [1301800314](#) , 1/2" NPT MAX-LOC Gasket [1300990149](#)

**Physical**

Approximate Break Strength N/A  
Bale Length N/A  
Body Style Straight  
Cable Diameter 5.54x10.69mm (.218x.421") Oval  
Color - Grommet N/A  
Gender Male  
Material - Body Nylon  
Material - Grip N/A  
Mesh Length N/A  
Number of Holes 1  
Thread Size 1/2" NPT

**Material Info**

Engineering Number 5580



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130098 Series](#)