

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300980200](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 7.37mm (.290")

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159  
 UL E76954

**General**

Product Family Cable Grips  
 Series [130098](#)  
 Comments Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required., Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.  
 Exclude SD Check Yes  
 Eye Type N/A  
 NEMA Rating NEMA 6P  
 O-Ring Yes  
 Overview [Strain-Relief Cord Grips](#)  
 Product Literature Order No 987651-6081  
 Product Name MAX-LOC  
 Type Strain Relief Grip  
 UPC 78678818946  
 Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#)

**Physical**

Approximate Break Strength N/A  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 7.37mm (.290")  
 Color - Grommet Yellow  
 Gender Male  
 Material - Body Nylon  
 Material - Grip N/A  
 Mesh Length N/A  
 Net Weight 37.194/g  
 Number of Holes 2  
 Thread Size 1/2" NPT

**Material Info**

Engineering Number 5594-006W

**Reference - Drawing Numbers**

Sales Drawing SD-130098-196



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130098 Series](#)