

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990190](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC/Watertite Cord Grips, 1/2" NPT, Straight Male, Body Size F2 5 3/4", Cable Diameter 12.70-15.88mm

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Grips
Series	130099
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	N/A
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC, Watertite
Type	Strain Relief Grip
UPC	78678831512
Use With	1/2" NPT MAX-LOC Lock Nut 1300990143 , MAX-LOC O-Ring, 1/2" NPT 1301800314 , 1/2" NPT MAX-LOC Gasket 1300990149

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	14.22-16.00mm (.560-.630")
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Net Weight	0.034/kg
Number of Holes	1
Thread Size	1/2" NPT

Material Info

Engineering Number 5648M

Reference - Drawing Numbers

Sales Drawing SD-130099-007



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130099 Series](#)