

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301020084](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway Rubber Hand Lamp with 100W, Quick Open Guard with Reflector, with Switch, Cord Length 7.62m (25.0'), Cord Type 16/3 SOOW

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR85374

**General**

Product Family      Portable Lighting  
 Series      [130102](#)  
 Exclude SD Check      Yes  
 NEMA Configuration      NEMA 5-15  
 Outlet      None  
 Overview      [Hand Lamps](#)  
 Product Literature Order No      987650-8053  
 Product Name      Super-Safeway  
 Type      Hand Lamps  
 UPC      78678879408

**Physical**

Cord Length - Primary      7.62m (25.0')  
 Cord Length - Secondary      N/A  
 Depth      101.60mm (4.000")  
 Duty      Industrial  
 Guard Included      Yes  
 Guard Type      Quick Open, Reflector  
 Height      374.65mm (14.750")  
 Length      N/A  
 Material - Guard      #8 Gauge Zinc-plated Steel  
 Mounting Style      Hand Held  
 Packaging Type      Carton  
 Socket Construction      N/A

**Electrical**

Bulb Type      Incandescent  
 Cord Type - Primary      16/3 SOOW  
 Lamp Type      A21  
 Lamp Wattage - Maximum      100W  
 Lumens      1000  
 On/Off Switch      Yes  
 Voltage (Fixture) - Maximum      240V

**Material Info**

Engineering Number      105SA163



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130102 Series](#)