

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020171](#)
Status: **Active**
Overview: Hand Lamps
Description: Super-Safeway Rubber Hand Lamp with 100W, Open End Guard with Reflector, with Receptacle

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374
UL E59251

General

Product Family Portable Lighting
Series 130102
Exclude SD Check Yes
NEMA Configuration N/A
Outlet Side
Overview Hand Lamps
Product Literature Order No 987650-8053
Product Name Super-Safeway
Type Hand Lamps
UPC 78678860480

Physical

Cord Length - Primary N/A
Cord Length - Secondary N/A
Depth 153.92mm (6.060")
Duty Industrial
Guard Included Yes
Guard Type Open End, Reflector
Height 311.66mm (12.270")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Net Weight 439.077/g
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 114U



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130102 Series