

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040033](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Haztex Hazardous Location 26W Fluorescent Hand Lamp with 16/3 SOOW Cord Type, Cord Length 15.24m (50.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA	LR39801
UL	E30252

General

Product Family	Portable Lighting
Series	130104
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL), Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
Exclude SD Check	Yes
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Specialty Lighting
Product Literature Order No	987650-8052
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861269

Physical

Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	100.08mm (3.940")
Duty	Hazardous
Guard Included	Yes
Guard Type	Cast Aluminum
Height	482.60mm (19.000")
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	16/3 SOOW
Lamp Type	PL-C 26/41/4P
Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	1090-HZB163
--------------------	-------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130104 Series](#)

This document was generated on 09/19/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION