

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301040044](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W, 14/3 SOOW Cord Type, 15.24m (50.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR39801  
 UL                        E30252

**General**

Product Family                      Portable Lighting  
 Series                                  [130104](#)  
 Comments                              Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL), Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)  
 Exclude SD Check                      Yes  
 NEMA Configuration                      NEMA 5-15  
 NEMA Rating                              NEMA 4X  
 Outlet                                      None  
 Overview                                  [Specialty Lighting](#)  
 Product Literature Order No              987650-8052  
 Product Name                              Haztex  
 Type                                        Hand Lamps, Specialty Light  
 UPC                                         78678861434

**Physical**

Cord Length - Primary                      15.24m (50.0')  
 Cord Length - Secondary                      N/A  
 Depth                                      127.00mm (5.000")  
 Duty                                        Hazardous, Wet Location  
 Guard Included                              Yes  
 Guard Type                                  Cast Aluminum  
 Height                                        419.10mm (16.500")  
 Length                                        N/A  
 Material - Globe                              Tempered Soda-Lime Glass  
 Material - Guard                              Cast Aluminum  
 Mounting Style                              Hand Held  
 Packaging Type                              Carton  
 Socket Construction                        N/A

**Electrical**

Bulb Type                                      Incandescent  
 Cord Type - Primary                        14/3 SOOW  
 Lamp Type                                      A21  
 Lamp Wattage - Maximum                      100W  
 Lumens                                        1000  
 On/Off Switch                                  No  
 Voltage (Fixture) - Maximum                      120VAC 60 HZ

**Material Info**

Engineering Number                        61430B143



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130104 Series](#)

This document was generated on 09/18/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**