

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301060117](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets, NEMA L5-20 Plug, Overall Length 15.24m (50.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130106
Exclude SD Check	Yes
NEMA Configuration	NEMA L5-20
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Literature Order No	987650-8055
Product Name	Super-Safeway
Type	String Lights
UPC	78678879898

Physical

Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	107.95mm (4.250")
Length	15.24m (50.0')
Material - Guard	N/A
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded

Electrical

Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	323534
--------------------	--------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130106 Series](#)