

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080091](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway 4W Fluorescent Hand Lamp with Cord Ballast Location and no Switch, Cord Type 18/3 SJTW, Cord Length 5.49m (18.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130108
Exclude SD Check	Yes
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Literature Order No	987650-8053
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678861231

Physical

Cord Length - Primary	5.49m (18.0')
Cord Length - Secondary	N/A
Depth	31.75mm (1.250")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	342.90mm (13.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTW
Lamp Type	F4/T5
Lamp Wattage - Maximum	4W
Lumens	95
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	1045
--------------------	------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130108 Series](#)