

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100022](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway 500W Halogen Floodlight, Magnet Mount, with Guard, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130110](#)
 Exclude SD Check Yes
 NEMA Configuration NEMA 5-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Wide-Area Lighting Products](#)
 Product Literature Order No 987650-8054
 Product Name Super-Safeway
 Type Wide Area Lamps
 UPC 78678885061

Physical

Cord Length - Primary 7.62m (25.0')
 Cord Length - Secondary N/A
 Depth N/A
 Duty Industrial
 Guard Included Yes
 Guard Type Steel
 Height 374.65mm (14.750")
 Length 279.40mm (11.000")
 Material - Globe Tempered Glass
 Material - Guard #8 Gauge Zinc-plated Steel
 Mounting Style Magnet
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
 Cord Type - Primary 16/3 SOOW
 Lamp Type T-3 RSC
 Lamp Wattage - Maximum 500W
 Lumens 9200
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 8506M



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130110 Series](#)