

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301100034](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Wet Location 70W Metal Halide Magnet Mount Area Light with Feed Thru, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

UL      E174254

**General**

Product Family      Portable Lighting  
 Series      [130110](#)  
 Exclude SD Check      Yes  
 NEMA Configuration      NEMA 5-15  
 NEMA Rating      NEMA 3  
 Outlet      Feed-Through  
 Overview      [Wide-Area Lighting Products](#)  
 Product Literature Order No      987650-8054  
 Product Name      Woodhead  
 Type      Wide Area Lamps  
 UPC      78678829572

**Physical**

Cord Length - Primary      3.04m (10.0')  
 Cord Length - Secondary      0.305m (1.0')  
 Depth      207.26mm (8.160")  
 Duty      Wet Location  
 Guard Included      No  
 Guard Type      N/A  
 Height      264.16mm (10.400")  
 Length      228.60mm (9.000")  
 Material - Globe      Clear Polycarbonate  
 Material - Guard      N/A  
 Mounting Style      Magnet  
 Net Weight      5597.325/g  
 Packaging Type      Carton  
 Socket Construction      N/A

**Electrical**

Bulb Type      Metal Halide - Probe Start  
 Cord Type - Primary      16/3 SJTOW  
 Cord Type - Secondary      16/3 SJTOW  
 Lamp Type      MH70  
 Lamp Wattage - Maximum      70W  
 Lumens      3600  
 On/Off Switch      No  
 Voltage (Fixture) - Maximum      120VAC 60 HZ

**Material Info**

Engineering Number      8565F-MH



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130110 Series](#)