

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301110027](#)  
**Status:** **Active**  
**Overview:** [Stringlights](#)  
**Description:** Safety Yellow Molded Stringlight, 200W, 14/2 SJTW with 2.43m Lead 10 Sockets Guards Lamp-it-in-the-Box, Overall Length 30.48m (100.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

UL      E112216

**General**

Product Family      Portable Lighting  
 Series      [130111](#)  
 Exclude SD Check      Yes  
 NEMA Configuration      NEMA 1-15  
 NEMA Rating      Rain Tight  
 Outlet      None  
 Overview      [Stringlights](#)  
 Product Literature Order No      987650-8055  
 Product Name      Safety Yellow  
 Type      String Lights  
 UPC      78678840867

**Physical**

Cord Length - Primary      2.43m (8.0')  
 Cord Length - Secondary      0.61m (2.0')  
 Depth      N/A  
 Duty      Commercial  
 Guard Included      Yes  
 Guard Type      Polypropylene  
 Height      N/A  
 Length      30.48m (100.0')  
 Material - Guard      Polypropylene  
 Mounting Style      Stringer  
 Packaging Type      Carton  
 Socket Construction      Molded

**Electrical**

Bulb Type      Incandescent  
 Cord Type - Primary      14/2 SJTW  
 Lamp Type      A21  
 Lamp Wattage - Maximum      200W  
 Lumens      2000  
 On/Off Switch      No  
 Voltage (Fixture) - Maximum      120VAC 60 HZ

**Material Info**

Engineering Number      5000



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130111 Series](#)