

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301110030](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Safety Yellow Molded Stringlight, 200W, 12/3 SJTW with 2.43m Lead 10 Sockets Full Ground Ring, Overall Length 30.48m (100.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family Portable Lighting
Series [130111](#)
Exclude SD Check Yes
NEMA Configuration NEMA 5-15
NEMA Rating Rain Tight
Outlet None
Overview [Stringlights](#)
Product Literature Order No 987650-8055
Product Name Safety Yellow
Type String Lights
UPC 78678840869

Physical

Cord Length - Primary 2.43m (8.0')
Cord Length - Secondary 0.61m (2.0')
Depth N/A
Duty Commercial
Guard Included No
Guard Type N/A
Height N/A
Length 30.48m (100.0')
Material - Guard N/A
Mounting Style Stringer
Net Weight 2.700/kg
Packaging Type Carton
Socket Construction Molded

Electrical

Bulb Type Incandescent
Cord Type - Primary 12/3 SJTW
Lamp Type A21
Lamp Wattage - Maximum 200W
Lumens 2000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 5002



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130111 Series](#)