

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301250004](#)
Status: **Active**
Overview: Aero-Motive Wire-Rope Festoon Systems
Description: Wire Rope Festoon Car Flat

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Festoons
Series	130125
Cable Height - Maximum	6.86mm (.270")
Cable Width - Maximum	60.45mm (2.380")
Combined Cable Weight-Max./Car	4.08kg (9.0 lb)
Component Type	Car - Intermediate
Depth	51.40mm (2.024")
Duty	Light
Exclude SD Check	Yes
Height	127.00mm (5.000")
Length	115.06mm (4.530")
Overview	<u>Aero-Motive Wire-Rope Festoon Systems</u>
Product Name	Aero-Motive
Type	Wire Rope
UPC	78678863132

Physical

Material - Metal	N/A
Material - Resin	Nylon
Material - Wheel	Steel - Sealed Ball Bearing
Net Weight	220.445/g
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	35.05mm (1.380")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Flat

Material Info

Engineering Number	5111
--------------------	------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130125 Series](#)