

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301350216](#)  
**Status:** **Active**  
**Overview:** Outlet Boxes  
**Description:** Super-Safeway GFCI Multiple Outlet Box with Ground Continuity Monitor, Open Neutral Relay, (2) NEMA 5-15 Duplex with Flip Lids, 1.83m (6.0') Cord Length, 12/3 SOOW Cord, NEMA 5-15 Plug

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**General**

Product Family	Power Distribution
Series	<a href="#">130135</a>
Enclosure Rating	NEMA 4
Exclude SD Check	Yes
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<a href="#">Outlet Boxes</a>
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	GFCI Multiple Outlet Box
UPC	78678876129

**Physical**

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	Yes
Ground Continuity Monitor	Yes
NEMA Configuration	NEMA 5-15
Voltage - Maximum	120V

**Material Info**

Engineering Number	32GM15L123
--------------------	------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130135 Series](#)