

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360034](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multi-Tap 3-Phase to Single Phase, (3) Outlet Box with Buss Bars, NEMA 5-15

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General

| | |
|-----------------------------|------------------------------|
| Product Family | Power Distribution |
| Series | 130136 |
| Enclosure Rating | N/A |
| Exclude SD Check | Yes |
| GFCI Reset | N/A |
| Mounting Style | Portable |
| Open Neutral Relay | N/A |
| Overview | Outlet Boxes |
| Product Literature Order No | 987650-7737 |
| Product Name | Super-Safeway |
| Receptacle Type | Triple |
| Type | Multi-Tap and Strip Cordset |
| UPC | 78678831500 |

Physical

| | |
|-----------------------|---------------------------|
| Cord Diameter | 8.26-16.64mm (.325-.655") |
| Cord Grip Body Size | Double C-Clamp |
| Cord Length | N/A |
| Feed-Thru | No |
| Flip Lid | No |
| Material - Housing | Rubber |
| Number of Receptacles | 3 |
| Packaging Type | Carton |

Electrical

| | |
|-------------------------------|-----------|
| Cord Type | N/A |
| Current - Maximum per Contact | N/A |
| GFCI | No |
| Ground Continuity Monitor | No |
| NEMA Configuration | NEMA 5-15 |
| Voltage - Maximum | 120V |

Material Info

| | |
|--------------------|--------|
| Engineering Number | 315933 |
|--------------------|--------|



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130136 Series](#)