

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301360037](#)  
**Status:** **Active**  
**Overview:** [Outlet Boxes](#)  
**Description:** Super-Safeway Multi-Tap (3) NEMA 5-15 Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 14/3 SJOW Cord, NEMA 5-15 Plug, In-line GFCI

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837

**General**

Product Family      Power Distribution  
 Series      [130136](#)  
 Enclosure Rating      N/A  
 Exclude SD Check      Yes  
 GFCI Reset      Manual  
 Mounting Style      Portable  
 Open Neutral Relay      Yes  
 Overview      [Outlet Boxes](#)  
 Product Literature Order No      987650-7737  
 Product Name      Super-Safeway  
 Receptacle Type      Triple  
 Type      Multi-Tap and Strip Cordset  
 UPC      78678801252

**Physical**

Cord Diameter      9.65mm (.380")  
 Cord Grip Body Size      Double C-Clamp  
 Cord Length      7.62m (25.0')  
 Feed-Thru      No  
 Flip Lid      No  
 Material - Housing      Rubber  
 Number of Receptacles      3  
 Packaging Type      Bag

**Electrical**

Cord Type      14/3 SJOW  
 Current - Maximum per Contact      15.0A  
 GFCI      Yes-In-line  
 Ground Continuity Monitor      No  
 NEMA Configuration      NEMA 5-15  
 Voltage - Maximum      120V

**Material Info**

Engineering Number      31593A143IN



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130136 Series](#)