

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301360038](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multi-Tap (3) NEMA 5-15 Outlet Box with Buss Bars, 15.24m (50.0') Cord Length, 12/3 SOOW Cord, NEMA 5-15 Plug

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Power Distribution
 Series [130136](#)
 Enclosure Rating N/A
 Exclude SD Check Yes
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Outlet Boxes](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type Triple
 Type Multi-Tap and Strip Cordset
 UPC 78678879631

Physical

Cord Diameter 15.24mm (.600")
 Cord Grip Body Size Double C-Clamp
 Cord Length 15.24m (50.0')
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 3
 Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 120V

Material Info

Engineering Number 31593B123



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130136 Series](#)