

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370090](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-20 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, 5-20 Plug

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E38085

General

Product Family Power Distribution
Series [130137](#)
Enclosure Rating N/A
Exclude SD Check Yes
GFCI Reset N/A
Mounting Style Portable
Open Neutral Relay N/A
Overview [Outlet Boxes](#)
Product Literature Order No 987650-7737
Product Name Super-Safeway
Receptacle Type Duplex
Type Multiple Outlet Box
UPC 78678834771

Physical

Cord Diameter 15.24mm (.600")
Cord Grip Body Size Double C-Clamp
Cord Length 7.62m (25.0')
Feed-Thru No
Flip Lid No
Material - Housing Rubber
Number of Receptacles 2
Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
Current - Maximum per Contact 20.0A
GFCI No
Ground Continuity Monitor No
NEMA Configuration NEMA 5-20
Voltage - Maximum 125V

Material Info

Engineering Number 3000-10A123



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

ELV

Not Reviewed

RoHS Phthalates

Not Relevant

Not Reviewed

Search Parts in this Series

[130137 Series](#)