

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370097](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 15.24m (50.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating N/A
 Exclude SD Check Yes
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Outlet Boxes](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type Duplex
 Type Multiple Outlet Box
 UPC 78678879622

Physical

Cord Diameter 13.59mm (.535")
 Cord Grip Body Size Double C-Clamp
 Cord Length 15.24m (50.0')
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 2
 Packaging Type Carton

Electrical

Cord Type 14/3 SOOW
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 3000-1B143



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION