

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370102](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 1.83m (6.0') Cord Length, 14/3 SOOW Cord w In-Line GFCI, 5-15 Plug

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

| | |
|-----------------------------|---|
| Product Family | Power Distribution |
| Series | 130137 |
| Enclosure Rating | N/A |
| Exclude SD Check | Yes |
| GFCI Reset | Manual |
| Mounting Style | Portable |
| Open Neutral Relay | Yes |
| Overview | Watertite Wet-Location Wiring Solutions |
| Product Literature Order No | 987650-7737 |
| Product Name | Super-Safeway |
| Receptacle Type | Duplex |
| Type | Multiple Outlet Box |
| UPC | 78678879607 |

Physical

| | |
|-----------------------|-----------------|
| Cord Diameter | 13.59mm (.535") |
| Cord Grip Body Size | Double C-Clamp |
| Cord Length | 1.83m (6.0') |
| Feed-Thru | No |
| Flip Lid | No |
| Material - Housing | Rubber |
| Number of Receptacles | 2 |
| Packaging Type | Bag |

Electrical

| | |
|-------------------------------|-------------|
| Cord Type | 14/3 SOOW |
| Current - Maximum per Contact | 15.0A |
| GFCI | Yes-In-line |
| Ground Continuity Monitor | No |
| NEMA Configuration | NEMA 5-15 |
| Voltage - Maximum | 120V |

Material Info

Engineering Number 3000-1L143IN



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)