

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370153](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway Multiple Outlet Box, Ext Depth, Feed-Thru, (1) NEMA 5-15 GFCI Receptacle with Flip Lid, Open Neutral Relay, 0.91m 12/3 SOOW Cord on Both sides, 5-15 Plug & Conn

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837

**General**

Product Family	Power Distribution
Series	<a href="#">130137</a>
Enclosure Rating	NEMA 4
Exclude SD Check	Yes
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<a href="#">Watertite Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	GFCI Duplex
Type	Multiple Outlet Box
UPC	78678802524

**Physical**

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	1
Packaging Type	Carton

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	125V

**Material Info**

Engineering Number      3070F-GFI



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)