

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370178](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, Feed-Thru F3 (3/4"), (1) NEMA 5-15 GFCI Receptacles with Flip Lid, Open Neutral Relay, Top-of-Box GCM, 0.91m 12/3 SOOW Cord on Both sides, 5-15 Plug & Conn.

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating NEMA 4
 Exclude SD Check Yes
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type GFCI Duplex
 Type Multiple Outlet Box
 UPC 78678875165

Physical

Cord Diameter 15.24mm (.600")
 Cord Grip Body Size F3 3/4"
 Cord Length 1.83m (6.0')
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 1
 Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 15.0A
 GFCI Yes
 Ground Continuity Monitor Yes
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 3080F-GFI



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)