

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370214](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway Factory-Wired, 3-Phase Stringer Set, 2-Sided, One Box/Phase on 3.05m Center, Color-Coded NEMA 5-20 Receptacles, 12/5 SOW Cord, L21-20 Plug

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837

**General**

Product Family	Power Distribution
Series	<a href="#">130137</a>
Enclosure Rating	N/A
Exclude SD Check	Yes
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	<a href="#">Watertite Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	3-Phase Stringer Set
UPC	78678874569

**Physical**

Cord Diameter	18.03mm (.710")
Cord Grip Body Size	F3 3/4"
Cord Length	9.14m (30.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	12
Packaging Type	Carton

**Electrical**

Cord Type	12/5 SOW
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	125V

**Material Info**

Engineering Number      3095-002



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)