

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130137-0241](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: [Watertite® GFCI Coverplate Module for FS/FD Boxes, Clear Silicone, 20A/125V](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Power Distribution
Series	130137
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	Watertite® Wet-Location Wiring Solutions
Product Name	Watertite®
Receptacle Type	N/A
Type	Multiple Outlet Box
UPC	78678809566
Woodhead	Yes

Physical

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	Silicone
Number of Receptacles	0
Packaging Type	Carton

Electrical

Cord Type	N/A
Current - Maximum per Contact	20A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	125V

Material Info

Old Part Number	3362GF
-----------------	--------

Reference - Drawing Numbers

Sales Drawing	SD-130137-002
---------------	---------------



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

130137Series