

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430088](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-20 125V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Wiring Devices
 Series [130143](#)
 Exclude SD Check Yes
 IP Rating N/A
 NEMA Configuration NEMA 5-20
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Literature Order No 987650-8068
 Product Name Super-Safeway
 Receptacle Type Single
 Specialty N/A
 Type Cordset
 UPC 78678870139

Physical

Flange No
 Flip Lid No
 Gender Male-Female
 Length 15.24m (50.0')
 Locking Blade No
 Poles 2-pole/3-wire

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 20.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 1433B123



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130143](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION