

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430245](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Cordset, 12 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L16-20, 3ø 480V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E38085

**General**

Product Family                      Wiring Devices  
 Series                                  [130143](#)  
 Exclude SD Check                      Yes  
 IP Rating                                IP67  
 NEMA Configuration                      NEMA L16-20  
 Overview                                [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No              987650-8067  
 Product Name                              Watertite  
 Receptacle Type                          Single  
 Specialty                                N/A  
 Type                                        Cordset  
 UPC                                        78678871266

**Physical**

Cord Grip Body Size                      F3 3/4"  
 Flange                                      No  
 Flip Lid                                      No  
 Gender                                      Male-Female  
 Length                                      7.62m (25.0')  
 Locking Blade                              Yes  
 Poles                                        3-pole/4-wire

**Electrical**

Cord Type                                  12/3 SOOW  
 Current - Maximum per Contact              20.0A  
 GFCI                                        No  
 Lighted Connector                          No  
 Voltage - Maximum                          3ø 480V

**Material Info**

Engineering Number                          26W76A124



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143 Series](#)