

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460125](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Watertite Duplex Receptacle with Flip Coverplate, 2 Pole/3 Wire, NEMA 5-20, 125V

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E68122

General

Product Family [Wiring Devices](#)
 Series [130146](#)
 IP Rating IP67
 NEMA Configuration NEMA 5-20
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Name Watertite
 Receptacle Type Duplex
 Specialty N/A
 Type Receptacle
 UPC 78678871432

Physical

Flange No
 Flip Lid Yes
 Gender Female
 Length N/A
 Locking Blade No
 Net Weight 486.251/g
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 20.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 60W33DPLX

Reference - Drawing Numbers

Sales Drawing 1301460125-000



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130146 Series](#)