

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470058](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L15-20, 3Ø 250V, F3

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837

**General**

Product Family      Wiring Devices  
 Series      [130147](#)  
 Exclude SD Check      Yes  
 IP Rating      IP67  
 NEMA Configuration      NEMA L15-20  
 Overview      [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No      987650-8067  
 Product Name      Watertite  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678871373

**Physical**

Cord Grip Body Size      F3 3/4"  
 Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      Yes  
 Poles      3-pole/4-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      20.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      3Ø 250V

**Material Info**

Engineering Number      27W75MB



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)