

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470149](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L15-20 3ø 250V

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E46237

**General**

Product Family [Wiring Devices](#)  
 Series [130147](#)  
 Exclude SD Check Yes  
 IP Rating IP67  
 NEMA Configuration NEMA L15-20  
 Overview [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No 987650-8067  
 Product Name Watertite  
 Receptacle Type Single  
 Specialty N/A  
 Type Receptacle  
 UPC 78678871570

**Physical**

Flange No  
 Flip Lid Yes  
 Gender Female  
 Length N/A  
 Locking Blade Yes  
 Net Weight 407.325/g  
 Poles 3-pole/4-wire

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 20.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 3Ø 250V

**Material Info**

Engineering Number 67W75

**Reference - Drawing Numbers**

Sales Drawing 1301470149-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)