

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530022](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Molded NEMA 5-15, 15A, 120V, 7.62m (25.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E66308

**General**

Product Family                      Power Distribution  
 Series                                  [130153](#)  
 Enclosure Rating                      NEMA 4  
 Exclude SD Check                      Yes  
 GFCI Reset                              Manual  
 Mounting Style                        Portable  
 Open Neutral Relay                    Yes  
 Overview                                [Ground Fault Circuit Interrupter \(GFCI\) Products](#)  
 Product Literature Order No        987650-7737  
 Product Name                         Safeway  
 Receptacle Type                       N/A  
 Type                                      GFCI Commercial Duty, Single Phase  
 UPC                                        78678828403

**Physical**

Cord Diameter                        9.40mm (.370")  
 Cord Grip Body Size                Internal Double C-Clamp  
 Cord Length                         7.62m (25.0')  
 Feed-Thru                              Yes  
 Flip Lid                                 No  
 Material - Housing                    Nylon  
 Number of Receptacles              1  
 Packaging Type                        Bag

**Electrical**

Cord Type                                14/3 SJTW  
 Current - Maximum per Contact    15.0A  
 GFCI                                      Yes-In-line  
 Ground Continuity Monitor        No  
 NEMA Configuration                NEMA 5-15  
 Voltage - Maximum                 120V AC

**Material Info**

Engineering Number                 15050-25



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130153](#) Series