

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530093](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway Right-Angle Industrial GFCI, Portable, Single Phase, Automatic Reset, Molded NEMA 5-15 Tri-Tap, 15A, 120V, 0.61m (2.0') Cord Length

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 3R
 Exclude SD Check Yes
 GFCI Reset Automatic
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview Ground Fault Circuit Interrupter (GFCI) Products
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type N/A
 Type GFCI Industrial Duty, Single Phase
 UPC 78678888245

Physical

Cord Diameter 10.92mm (.430")
 Cord Grip Body Size Internal Double C-Clamp
 Cord Length 0.61m (2.0')
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Nylon
 Number of Receptacles 3
 Packaging Type Carton

Electrical

Cord Type 12/3 SJTW
 Current - Maximum per Contact 15.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 15054-1TTA

Reference - Drawing Numbers

Sales Drawing SD-130153-018



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)