

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530100](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway Right-Angle Industrial GFCI, Portable, Single Phase, Manual Reset, Molded NEMA 5-15, 15A, 120V, No Cord

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 3R
 Exclude SD Check Yes
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway
 Receptacle Type N/A
 Type GFCI Industrial Duty, Single Phase
 UPC 78678889767

Physical

Cord Diameter N/A
 Cord Grip Body Size Internal Double C-Clamp
 Cord Length N/A
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Nylon
 Net Weight 181.436/g
 Number of Receptacles 0
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 15054M

Reference - Drawing Numbers

Sales Drawing SD-130153-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)