

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530113](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, 1433 Plug, 1533 Receptacle, 20A, 120V, 0.61m (2.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
Series [130153](#)
Enclosure Rating NEMA 4X
Exclude SD Check Yes
GFCI Reset Manual
Mounting Style Portable
Open Neutral Relay Yes
Overview Ground Fault Circuit Interrupter (GFCI) Products
Product Literature Order No 987650-7737
Product Name Super-Safeway
Receptacle Type N/A
Type GFCI Industrial Duty, Single Phase
UPC 78678889743

Physical

Cord Diameter 10.67mm (.420")
Cord Grip Body Size Internal Double C-Clamp
Cord Length 0.61m (2.0')
Feed-Thru Yes
Flip Lid No
Material - Housing Nylon
Net Weight 897.204/g
Number of Receptacles 1
Packaging Type Bag

Electrical

Cord Type 12/3 SJEOOW
Current - Maximum per Contact 20.0A
GFCI Yes-In-line
Ground Continuity Monitor No
NEMA Configuration NEMA 5-20
Voltage - Maximum N/A

Material Info

Engineering Number 20051-1M



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130153](#) Series