

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530155](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA L6-20 Plug & Connector, 20A, 240V, 0.61m (2.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4X
Exclude SD Check	Yes
GFCI Reset	Automatic
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<u>Ground Fault Circuit Interrupter (GFCI) Products</u>
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78678888290

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag

Electrical

Cord Type	12/3 SJEOOW
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA L6-20
Voltage - Maximum	120V

Material Info

Engineering Number 24052-1A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)