

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530157](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Molded NEMA L6-20 Plug & Connector, 20A, 240V, 0.61m (2.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4X
Exclude SD Check	Yes
GFCI Reset	Automatic
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78678888289

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag

Electrical

Cord Type	12/3 SJEOOW
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA L6-20
Voltage - Maximum	120V

Material Info

Engineering Number 24052-1MLDA



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)