

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530163](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA L5-30, 30A, 120V, 0.61m (2.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E66308

**General**

Product Family	Power Distribution
Series	<a href="#">130153</a>
Enclosure Rating	NEMA 6P
Exclude SD Check	Yes
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<a href="#">Ground Fault Circuit Interrupter (GFCI) Products</a>
Product Literature Order No	987650-7737
Product Name	Safeway
Receptacle Type	N/A
Type	GFCI Commercial Duty, Single Phase
UPC	78678835072

**Physical**

Cord Diameter	13.00mm (.512")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag

**Electrical**

Cord Type	10/3 SJTW
Current - Maximum per Contact	30.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA L5-30
Voltage - Maximum	120V

**Material Info**

Engineering Number	30051-1
--------------------	---------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130153 Series](#)