

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301540052](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 6-20, 250V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LL52750

**General**

Product Family      Wiring Devices  
 Series      [130154](#)  
 Exclude SD Check      Yes  
 IP Rating      IP67  
 NEMA Configuration      NEMA 6-20  
 Overview      [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No      987650-8067  
 Product Name      Watertite  
 Receptacle Type      Duplex  
 Specialty      N/A  
 Type      Molded Y Cordset  
 UPC      78678800610

**Physical**

Cord Grip Body Size      F2 1/2"  
 Flange      No  
 Flip Lid      No  
 Gender      Male-Female  
 Length      0.91m (3.0')  
 Locking Blade      No  
 Poles      2-pole/3-wire

**Electrical**

Cord Type      12/3 SOOW  
 Current - Maximum per Contact      20.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      250V

**Material Info**

Engineering Number      14W48-Y



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130154 Series](#)