

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301550154](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Watertite Connector with California Style Locking Blade, 2 Pole/3 Wire, Non-NEMA, 250V, Cord Grip Body Size F5

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130155](#)
 Exclude SD Check Yes
 IP Rating IP67
 NEMA Configuration Non-NEMA Locking CA
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-8067
 Product Name Watertite
 Receptacle Type Single
 Specialty N/A
 Type Connector
 UPC 78678801460

Physical

Cord Grip Body Size F5 1 1/4"
 Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade Yes
 Net Weight 125.644/g
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 50.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 250V

Material Info

Engineering Number CS82W64



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130155 Series](#)