

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130143-0129](#)
Status: **Active**
Overview: Watertite® Wet-Location Wiring Solutions
Description: Watertite® Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMANEMA 5-20 125V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA	LR6837
UL	E38085

General

Product Family	Wiring Devices
Series	130143
IP Rating	IP67
NEMA Configuration	NEMA 5-20
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite®
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678871009
Woodhead	Yes

Physical

Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	30.48m (100.0')
Locking Blade	No
Poles	2-pole/3-wire

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	20A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

Material Info

Old Part Number	14W33D123
-----------------	-----------



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130143Series