

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130091-0025](#)  
**Status:** **Active**  
**Overview:** [Electric Reels](#)  
**Description:** Woodhead® Standard Cord Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 15A GFCI Pendant Outlet Box, One Duplex, NEMA 5-15 Outlet

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**General**

Product Family	Electric Reels
Series	130091
Cable Length	0.457m (1.50')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.36m (14.25")
NEMA Configuration	NEMA 5-15
Overview	<a href="#">Electric Reels</a>
Product Literature Order No	987650-8061
Product Name	Super-Safeway™
Type	Cord Reel
UPC	78678833616
Width	196.85mm (7.750")
Woodhead	Yes

**Physical**

Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Net Weight	131.540/kg
Number of Conductors	3
Number of Receptacles	2
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	16

**Electrical**

Bulb Included	N/A
Cord Type	16/3 SJTOW
Current - Maximum per Contact	8A
GFCI	Yes
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V

**Material Info**

Old Part Number	980-3070G
-----------------	-----------



**EU RoHS**

**Not RoHS Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

130091Series

This document was generated on 10/08/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**