

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130147-0144](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite® Receptacle with Locking Blade, Single Flip Coverplate, 2 Pole/3 Wire, NEMA L6-20 250V

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

UL E46237

General

Product Family	Wiring Devices
Series	130147
IP Rating	IP67
NEMA Configuration	NEMA L6-20
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite®
Receptacle Type	Single
Specialty	N/A
Type	Receptacle
UPC	78678871560
Woodhead	Yes

Physical

Cord Grip Body Size	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	Yes
Net Weight	453.590/g
Poles	2-pole/3-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	20A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V

Material Info

Old Part Number	67W48
-----------------	-------



EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
 Not Reviewed
Low-Halogen Status
 Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130147Series