

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130143-0113](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway® Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-15, 125V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E38085

**General**

Product Family [Wiring Devices](#)  
 Series [130143](#)  
 IP Rating N/A  
 NEMA Configuration NEMA 5-15  
 Overview [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No 987650-8068  
 Product Name Super-Safeway™  
 Receptacle Type Single  
 Specialty N/A  
 Type Cordset  
 UPC 78678879552  
 Woodhead Yes

**Physical**

Cord Grip Body Size N/A  
 Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 30.48m (100.0')  
 Locking Blade No  
 Poles 2-pole/3-wire

**Electrical**

Cord Type 16/3 SOOW  
 Current - Maximum per Contact 15A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 125V

**Material Info**

Old Part Number 1447D163



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC  
Not Reviewed**

**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130143Series](#)