

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1201080272](#)  
**Status:** **Active**  
**Overview:** Brad® Industrial Ethernet Solutions  
**Description:** Industrial Ethernet Double-Ended RJ-45 Cordset, Male (Straight) to Male (Straight), 22 AWG, Shielded PUR Cable, 6.0m (19.68') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120108</a>
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP67
Material - Contact	N/A
Overview	<a href="#">Brad® Industrial Ethernet Solutions</a>
Performance Category	5e
Product Name	Industrial Ethernet
Protocol	EtherNet
Region	America, Asia, Europe
Type	Double Ended
UPC	78172536955

**Physical**

Cable Diameter	6.70mm (.264")
Cable Length	6.0m (19.68')
Color - Cable Jacket	Green
Coupling Style	Threaded
Gender	Male-Male
Keyway	N/A
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Orientation	Straight to Straight
Poles	N/A
Temperature Range - Operating	-20°C to +60°C
Wire Size AWG	22
Wire/Cable Type	Shielded PUR

**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

**Material Info**

Engineering Number	E66A06011M060
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-120108-044
---------------	---------------

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[120108 Series](#)