

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130099-0097](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** MAX-LOC® Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625"), Non-Metallic Mesh

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159  
 UL E76954

**General**

Product Family Cable Grips  
 Series [130099](#)  
 Eye Type N/A  
 NEMA Rating NEMA 3R  
 O-Ring No  
 Overview [Strain-Relief Cord Grips](#)  
 Product Literature Order No 987650-8064  
 Product Name MAX-LOC®  
 Type Strain Relief Grip  
 UPC 78678855385  
 Use With 3/4" NPT MAX-LOC® Lock Nut [130099-0144](#) , 3/4" NPT MAX-LOC® Gasket Sealing Ring [130099-0150](#) , 3/4" NPT MAX-LOC® O-Ring [130180-0333](#)  
 Woodhead Yes

**Physical**

Approximate Break Strength N/A  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 12.70-15.88mm (.500-.625")  
 Color - Grommet Gray  
 Gender Male  
 Material - Body Nylon  
 Material - Grip Nylon  
 Mesh Length N/A  
 Number of Holes 1  
 Thread Size 3/4" NPT

**Material Info**

Old Part Number 5538NM

**Reference - Drawing Numbers**

Sales Drawing SD-130099-005



image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Not Reviewed**  
**Low-Halogen Status Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130099Series](#)