

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1210120071](#)  
**Status:** **Active**  
**Overview:** mPm® DIN Valve Connectors  
**Description:** mPm® DIN Base, Form A, B26 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black Nitrile Gasket with Screw

**Documents:**

[Drawing \(PDF\)](#)      [Test Summary STR-1467-001 \(PDF\)](#)  
[Packaging Specification PK-121012-B26-001 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family      Field Attachable / Accessories  
Series      [121012](#)  
Form      A  
IP Rating      IP65, IP67  
Material - Contact      Brass  
Overview      [mPm® DIN Valve Connectors](#)  
Product Name      mPm®  
Type      Field Attachable Connector  
UPC      883906248741

**Physical**

Cable Diameter      N/A  
Coupling Type      N/A  
Diagnostics / LEDs      No  
Diagnostics Port      No  
Gender      N/A  
Keyway      None  
Material - Connector Body      Polypropylene  
Material - Coupling Nut      N/A  
Material - Plating Mating      Silver  
Net Weight      11.178/g  
Orientation      Straight  
Pitch - Mating Interface      18.00mm  
Poles      2  
Temperature Range - Operating      -40°C to +90°C  
Wire Size AWG      N/A

**Electrical**

Current - Maximum per Contact      16.0A  
Voltage - Maximum      250V AC / 300V DC

**Material Info**

Engineering Number      B262000N2

**Reference - Drawing Numbers**

Packaging Specification      PK-121012-B26-001  
Sales Drawing      SD-121012-002-000  
Test Summary      STR-1467-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per -ED/01/2017 (12 January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**  
[121012 Series](#)