

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1120260013](#)  
**Status:** **Active**  
**Overview:** PC Network Interface Cards  
**Description:** Direct-Link Gateway PROFIBUS DP Slave to Serial Modbus Master/Slave

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**General**

Product Family	Network Interface Cards
Series	<a href="#">112034</a>
Application	IO Control
Approvals	CE certified
Communication Speed	PROFIBUS 9.6 kbps to 12 Mbps, Serial: 600 to 57,600 bps
IP Rating	IP20
Mounting Style	DIN Rail
Operating System	N/A
Overview	<a href="#">PC Network Interface Cards</a>
Product Literature Order No	987651-4589
Product Name	Direct-Link®
Protocol	PROFIBUS, Serial
Protocol Detail	PROFIBUS* DPV0 Slave, Serial Free Send/Rec (ASCII/RT, Serial Modbus† RTU/ASCII Slave, Serial Modbus†RTU/ASCII Master)
Slot	None
Software Downloads	DRL-DPS-SRM
Type	PROFIBUS* Gateway, Serial Gateway
UPC	78678803634
Woodhead	Yes

**Physical**

Channels	2
Interface	DAServer, DDE Server, DLL, OPC DA
Net Weight	0.248/kg
Network Connection Type	PROFIBUS D-Sub Female (9 pin), Serial: Screw Terminal
Packaging Type	Carton
Processor	N/A
Temperature Range - Operating	0°C to +55°C

**Electrical**

EMC	N/A
Supply Voltage	24V

**Material Info**

Engineering Number	DRL-DPS-SRM
--------------------	-------------

**Reference - Drawing Numbers**

Sales Drawing	SD-112026-0013-001
---------------	--------------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[112034 Series](#)