

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1210120127](#)  
**Status:** **Active**  
**Overview:** mPm® DIN Valve Connectors  
**Description:** mPm® DIN Base, Form C - Micro, B39 Base, 3 Pole Plus Ground Terminal, 250V AC/300V DC, Black Nitrile Gasket with Screws

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-121012-B39-001 \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">121012</a>
Form	B - Industrial
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	<a href="#">mPm® DIN Valve Connectors</a>
Product Name	mPm®
Type	Field Attachable Connector
UPC	883906361099

**Physical**

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Tin
Orientation	Straight
Pitch - Mating Interface	11.00mm
Poles	3
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	10.0A
Voltage - Maximum	250V AC / 300V DC

**Material Info**

Engineering Number	B393000N0
--------------------	-----------

**Reference - Drawing Numbers**

Packaging Specification	PK-121012-B39-001
Sales Drawing	SD-121012-126

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[121012 Series](#)