

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130137-0128](#)
Status: **Active**
Overview: Watertite® Wet-Location Wiring Solutions
Description: Super-Safeway® Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 7.62m (25.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA	LR6837
UL	E38085

General

Product Family	Power Distribution
Series	130137
Enclosure Rating	NEMA 4
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	<u>Watertite® Wet-Location Wiring Solutions</u>
Product Literature Order No	987650-7737
Product Name	Super-Safeway™
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678879663
Woodhead	Yes

Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F2 1/2"
Cord Length	7.62m (25.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

Electrical

Cord Type	14/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	125V

Material Info

Old Part Number	3005-1A143
-----------------	------------



EU RoHS

Not RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130137Series](#)